# SpotTrack<sup>®</sup> prisms





## SpotTrack<sup>®</sup> prism configurations

The recommended targets for SpotTrack all use industry standard, high-quality prisms in sealed canisters. With three different configurations available – the eight-prism cluster, the single prism, and the single prism with yoke and magnetic mount – they cover a wide range of applications.

### **Technical specifications**

#### Prism specifications

Aperture Weight Glass material Beam deviation Canister material

Enclosure protection Threading Operating temp. range Storage temp. range

#### Angular coverage Single prism

Eight-prism cluster

62 mm 0.2 kg H-K9L < 5 arcseconds Black Zytel 101 nylon with 13% glass fill IP67 5/8 × 11 -30 °C - +50 °C -30 °C - +70 °C

ca. 45° horizontal ca. ±23° vertical ca. 180° horizontal ca. ±23° vertical

#### Yoke and magnetic mount

Tilt range of yoke Maximum pull of magnetic mount ±130° 54 kg on a 13 mm steel plate

#### Weight with mount

Single prism	
(rail & mast mount)	0.9 kg
Single prism	
(with yoke & magnetic mount)	0.9 kg
Eight-prism cluster	
(rail and mast mount)	2.8 kg

Specifications subject to change without any further notice.

Switchboard: +47 73 58 76 00 Global support: +47 33 03 24 07 seatex.sales@kd.kongsberg.com